

# Vivid™ Fogger

SF-FG02-220

**STREAMLINE**  
SPECIFICATION SHEET

## Vivid™ Fogging Machine, Effective & portable infection control system

This handheld portable unit can be used in a range of different environments - spanning from small areas to large and even outdoors. It is of vital use in the fight against infection and can offer a truly unique sanitisation solution wherever it is used.

- Liquid is atomised to create a very fine fog which binds to surfaces to disinfect on contact.
- Multiple spray nozzles produce different size droplets for various applications.
- Easy to carry and operate.
- Designed for disinfecting, sterilisation, air purification, anti-virus, disease preventions, and more.
- After using the foggers you only need to leave indoor areas for approx 60 mins afterwards and ventilated areas for only 20 minutes, before re-occupation.

### Ideal for use on:

- Public transport
- Emergency services vehicles
- Aircraft
- Lifts and stairwells with limited power supply
- Hospitals, clinics & veterinary surgeries
- Doctor surgeries, dentists & health centres
- Schools and colleges
- Equipment loan stores
- Nursing homes
- Delivery vehicles
- Ambulances
- Mortuaries
- Hotels, spas & gyms
- Internal play areas
- Office blocks, hotels, shops, cinemas
- High traffic internal pedestrian areas
- Shopping malls & precincts
- Public transport
- Train stations / bus stations

These are just some of the clients which find this unit indispensable for sanitising whole rooms and wards, wet rooms, lavatories, bathrooms, shower rooms, lifts, stairwells and communal areas.



Effective with the use of **Vivid™ SENSE Sanitising Solution** or similar certified products

### Specifications:

- |                   |   |
|-------------------|---|
| • Tank Capacity   | 2 Litres  |
| • Spraying volume | 50-260ml / min  |
| • Coverage        | Up to 20m <sup>2</sup> per minute<br>(Full tank can cover up to 600m <sup>2</sup> ) |
| • Spray time      | Full tank can provide up to 30 minutes<br>spray time*                               |
| • Particle Size   | 10-15 UM  |
| • Atomised volume | 50ml/min  |
| • Effective range | 6-8 metres  |
| • Weight          | 3.1Kgs  |
| • Power supply    | AC220V/50-60HZ  |
| • Power           | 800W  |

\*Based on fogging with a No 1 Nozzle. Coverage would depend entirely on how the operator is using the equipment.